



Transformer

by ABB





1M000000

Catalog Number **Type QL**
9T10C1196G31

150.0 KVA 60 HZ 3 PH 5.3 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 240 VOLTS (LINE-LINE)

JUMPER CONNECTION	
TAP	VOLTS
1-2	505
2-3	493
3-4	480
4-5	467
5-6	455
6-7	442
7-8	429



NET WGT	INSPECTION & FINAL TEST
1240 LB	
562.5 Kg	NOG
89686	N137!
DX76C	091021



LISTED 769G

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
 CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

X3 - X2 - X1 - -

- H3 - H2 - H1

Note: standard

Outline: 303B11GEDXP76C

X3 - X2 - X1 - - H1
 - H3 - H2 - H1
 X3 - X2 - X1 - -
 - H3 - H2 - H1

2M000000

3M000000