



Transformer

by ABB



1M000000


Catalog Number 9T10C1712 **Type** QL

30.0 KVA 60 HZ 3 PH 4 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C


Note: Design is based on 30.00KVA & 115C Rise 3.9% Imp.

PRIMARY (X) 220 VOLTS (LINE-LINE)
SECONDARY (H) 480 VOLTS (LINE-LINE)
277 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	TAP VOLTS
1	231
2	226
3	220
4	213
5	208
6	203
7	198



COIL TAP ARRANGEMENT



NET WGT
353 LB
160.1 Kg
89782
UX72C

INSPECTION & FINAL TEST
NOG
N139!
092021



LISTED 769G

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
 CHECK ADDITIONAL NEC AND LOCAL CODE

H3 X3 H2 X2 H1 X1 H0

Note: standard

Outline: 303B111GEUXP72C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

H3 X3 H2 X2 H1 X1 H0

H3 X3 H2 X2 H1 X1 H0

H3 X3 H2 X2 H1 X1 H0

2M000000

3M000000