



# Transformer

by ABB




\*1M000000\*

**Catalog Number** 9T10C1263G31 **Type** QL


45.0 KVA 60 HZ 3 PH 3.5 % IMP  
40 C AMB. 115 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)  
SECONDARY (X) 230 VOLTS (LINE-LINE)

JUMPER CONNECTION TAP	VOLTS
1	503
2	492
3	480
4	467
5	456
6	446
7	431



### COIL TAP ARRANGEMENT



**NET WGT**  
480 LB  
217.7 Kg  
88884  
UX73C

**INSPECTION & FINAL TEST**  
NOG  
N137!  
091021



X3 H3 X2 H2 X1 H1  
X3 H3 X2 H2 X1 H1

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
CHECK ADDITIONAL NEC AND LOCAL CODE

X3 H3 X2 H2 X1 H1 -  
- - - - -  
Note: standard

Outline: 303B111GEUXP73C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

