



Transformer

by ABB



1M000000



Catalog Number 9T10C1996 **Type** QL

150.0 KVA 60 HZ 3 PH 3.8 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 230 VOLTS (LINE-LINE)
SECONDARY (H) 400 VOLTS (LINE-LINE)
231 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION

TAP	VOLTS
1-2	243
2-3	237
3-4	230
4-5	225
5-6	218
6-7	212
7-8	206



NET WGT
1085 LB
492.2 Kg
89802
DY76C

INSPECTION & FINAL TEST
NOG
N139!
092021



LISTED 769G

H3 - H2 - H1 - -
- X3 - X2 - X1 -
H3 - H2 - H1 -
- X3 - X2 - X1 -

H0

2M000000

3M000000

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.

CHECK ADDITIONAL NEC AND LOCAL CODE

H3 - H2 - H1 - -
- X3 - X2 - X1 -

Note: H0 at the bottom

Outline: 303B111GEDYP76C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency