



# Transformer

by ABB



\*1M000000\*


**Catalog Number** 9T10C1345 **Type** QL

112.5 KVA 60 HZ 3 PH 6.4 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C


PRIMARY (X) 208 VOLTS (LINE-LINE)  
SECONDARY (H) 480 VOLTS (LINE-LINE)  
277 VOLTS (LINE-NEUTRAL)

**JUMPER CONNECTION**

TAP	VOLTS
1-2	220
2-3	214
3-4	208
4-5	204
5-6	199
6-7	193
7-8	188



**COIL TAP ARRANGEMENT**



**NET WGT**  
790 LB  
358.3 Kg  
89723  
DY75C

**INSPECTION & FINAL TEST**  
NOG  
N139!  
092021



LISTED 769G

H3 - H2 - H1 - -

- X3 - X2 - X1

H3 - H2 - H1 -

- X3 - X2 - X1

H0

\*2M000000\*

\*3M000000\*

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**

COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.

CHECK ADDITIONAL NEC AND LOCAL CODE

H3 - H2 - H1 - -

- X3 - X2 - X1

Note: H0 at the bottom

Outline: 303B111GEDYP75C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency