



# Transformer

by ABB



\*1M000000\*

**Catalog Number** 9T10C2093 **Type** QL

45.0 KVA 60 HZ 3 PH 3.4 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C


PRIMARY (H) 400 VOLTS (LINE-LINE)  
SECONDARY (X) 400 VOLTS (LINE-LINE)  
231 VOLTS (LINE-NEUTRAL)

**JUMPER CONNECTION**

TAP	VOLTS
1	419
2	411
3	400
4	390
5	379
6	372
7	361



### COIL TAP ARRANGEMENT



**NET WGT**  
480 LB  
217.7 Kg  
88898  
UX73C

**INSPECTION & FINAL TEST**  
NOG  
N137!  
091021



LISTED 769G

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
 CHECK ADDITIONAL NEC AND LOCAL CODE

X3 H3 X2 H2 X1 H1 -

Note: X0 at the top

Outline: 303B111GEUXP73C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

	X3	H3	X2	H2	X1	H1	-
	X3	H3	X2	H2	X1	H1	-

\*2M000000\*

\*3M000000\*