



Transformer

by ABB




1M000000

Catalog Number 9T10C1345G61 **Type** QL


112.5 KVA 60 HZ 3 PH 2.9 % IMP
40 C AMB. 80 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 208 VOLTS (LINE-LINE)
SECONDARY (H) 480 VOLTS (LINE-LINE)
277 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	TAP VOLTS
1-2	220
2-3	214
3-4	208
4-5	202
5-6	195
6-7	189
7-8	183



COIL TAP ARRANGEMENT



NET WGT 1085 LB 492.2 Kg	INSPECTION & FINAL TEST NOG N139! 092021
89727 DY76C	



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

H3 - H2 - H1 - -
- X3 - X2 - X1

Note: H0 at the bottom

Outline: 303B111GEDYP76C

H3 - H2 - H1 - -

- X3 - X2 - X1

H3 - H2 - H1 - -

- X3 - X2 - X1

H0

2M000000

3M000000