



# Transformer

—  
by ABB



\*1M000000\*


**Catalog Number**      **Type QL**  
**9T10C1347**

225.0 KVA    60 HZ    3 PH    3.2 % IMP  
40 C AMB.    150 C RISE    220 C SYSTEM    IS-19C


**JUMPER CONNECTION**

TAP	VOLTS
1-2	225
2-3	217
3-4	208
4-5	199
5-6	191

PRIMARY (X)      208 VOLTS (LINE-LINE)  
SECONDARY (H)    480 VOLTS (LINE-LINE)  
                              277 VOLTS (LINE-NEUTRAL)



**COIL TAP ARRANGEMENT**



**NET WGT**      **INSPECTION & FINAL TEST**  
1847 LB      837.8 Kg  
89732      **NOG**  
DX77C      N137!  
091021



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1077G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP009**  
COPPER CONDUCTOR      PRIMARY: 10 KV BIL      SECONDARY: 10 KV BIL  
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
CHECK ADDITIONAL NEC AND LOCAL CODE

Note:

Outline: 303B112GEDXP77C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



\*2M000000\*



\*3M000000\*