



Transformer

by ABB



1M000000


Catalog Number 9T10C2213 **Type** QL

45.0 KVA 60 HZ 3 PH 3.2 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C


Note: Design is based on 45.00KVA & 115C Rise 3% Imp.

PRIMARY (H) 460 VOLTS (LINE-LINE)
SECONDARY (X) 400 VOLTS (LINE-LINE)
231 VOLTS (LINE-NEUTRAL)

| JUMPER CONNECTION | TAP VOLTS |
|-------------------|-----------|
| 1 | 484 |
| 2 | 473 |
| 3 | 460 |
| 4 | 447 |
| 5 | 437 |
| 6 | 426 |
| 7 | 415 |



COIL TAP ARRANGEMENT



NET WGT
480 LB
217.7 Kg
88901
UX73C

INSPECTION & FINAL TEST
NOG
N137!
091021



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
 CHECK ADDITIONAL NEC AND LOCAL CODE

X3 H3 X2 H2 X1 H1 -

Note: X0 at the top

Outline: 303B111GEUXP73C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

X3 H3 X2 H2 X1 H1 -

X3 H3 X2 H2 X1 H1 -

X0

2M000000

3M000000