



Transformer

by ABB



1M000000


Catalog Number
9T10C2213G31

Type QL


45.0 KVA 60 HZ 3 PH 3 % IMP
40 C AMB. 115 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 460 VOLTS (LINE-LINE)
SECONDARY (X) 400 VOLTS (LINE-LINE)
 231 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	
TAP	VOLTS
1	484
2	473
3	460
4	447
5	437
6	426
7	415



COIL TAP ARRANGEMENT



NET WGT	INSPECTION & FINAL TEST
480 LB	
217.7 Kg	
88901	NOG
UX73C	N137!
	091021



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
 CHECK ADDITIONAL NEC AND LOCAL CODE

X3	H3	X2	H2	X1	H1	-
-	-	-	-	-	-	-

Note: X0 at the top

Outline: 303B111GEUXP73C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

	X3	H3	X2	H2	X1	H1	-
	X3	H3	X2	H2	X1	H1	-

2M000000

3M000000