



by ABB



\*1M000000\*


**Catalog Number** 9T10C2386 **Type** QL

150.0 KVA 60 HZ 3 PH 3.8 % IMP  
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C


PRIMARY (H) 600 VOLTS (LINE-LINE)  
SECONDARY (X) 480 VOLTS (LINE-LINE)  
277 VOLTS (LINE-NEUTRAL)

**JUMPER CONNECTION**

TAP	VOLTS
1-2	630
2-3	617
3-4	600
4-5	586
5-6	567
6-7	554
7-8	542



**COIL TAP ARRANGEMENT**



**NET WGT**  
1085 LB  
492.2 Kg  
89834  
DY76C

**INSPECTION & FINAL TEST**  
NOG  
N139!  
092021



LISTED 769G



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

X3 - X2 - X1 - -

- H3 - H2 - H1

Note: X0 at the bottom

Outline: 303B111GEDYP76C