



Transformer

—
by ABB




1M000000

Catalog Number **Type QL**
9T10C1392G31

30.0 KVA **60 HZ** **3 PH** **3.7 % IMP**
40 C AMB. **115 C RISE** **220 C SYSTEM** **IS-19C**

PRIMARY (X) **208 VOLTS (LINE-LINE)**
SECONDARY (H) **400 VOLTS (LINE-LINE)**
 231 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	
TAP	VOLTS
1	218
2	213
3	208
4	203
5	198
6	193
7	188




NET WGT
353 LB
160.1 Kg
89743
UX72C

INSPECTION & FINAL TEST
NOG
N139!
092021



COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

H3	X3	H2	X2	H1	X1	H0
-	-	-	-	-	-	-

Note: standard

Outline: 303B111GEUXP72C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

H3 X3 H2 X2 H1 X1 H0

2M000000

3M000000

H3 X3 H2 X2 H1 X1 H0