



# Transformer



\*1M000000\*

Catalog Number

Type QL


9T10C1776

150.0 KVA 60 HZ 3 PH 4.3 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 380 VOLTS (LINE-LINE)

SECONDARY (H) 480 VOLTS (LINE-LINE)



JUMPER CONNECTION	
TAP	VOLTS
1-2	398
2-3	392
3-4	380
4-5	373
5-6	360
6-7	354
7-8	341


NET WGT  
1085 LB  
492.2 Kg

60458  
DY76C

N0G  
022516

INSPECTION  
&  
FINAL TEST  
N609!

### COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

Outline:  
303B111GEDYP76C

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES  
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODE


H3 - H2 - H1 - -  
- X3 - X2 - X1

Note: standard

H3 - H2 - H1 - -  
- X3 - X2 - X1



\*2M000000\*



\*3M000000\*