



# Transformer

by ABB



\*1M000000\*

**Catalog Number** 9T10C1793G61 **Type** QL


45.0 KVA 60 HZ 3 PH 2.9 % IMP  
40 C AMB. 80 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 380 VOLTS (LINE-LINE)  
SECONDARY (X) 208 VOLTS (LINE-LINE)  
120 VOLTS (LINE-NEUTRAL)

| JUMPER CONNECTION | TAP VOLTS |
|-------------------|-----------|
| 1                 | 399       |
| 2                 | 390       |
| 3                 | 380       |
| 4                 | 369       |
| 5                 | 360       |
| 6                 | 352       |
| 7                 | 343       |



### COIL TAP ARRANGEMENT



**NET WGT**  
661 LB  
299.8 Kg  
89789  
UY74C

**INSPECTION & FINAL TEST**  
NOG  
N139!  
092021



LISTED 769G

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

ASSEMBLED IN MEXICO

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
 CHECK ADDITIONAL NEC AND LOCAL CODE

X3 H3 X2 H2 X1 H1

Note: X0 at the bottom

Outline: 303B111GEUY74C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

X3 H3 X2 H2 X1 H1  
 X3 H3 X2 H2 X1 H1  
 X0



\*2M000000\*



\*3M000000\*