



# Transformer



\*1M000000\*

X4

Catalog Number

Type QL


9T10W1186

150.0 KVA 60 HZ 3 PH 4.1 % IMP


40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

Note: Design is based on 150.0KVA & 150C Rise 4.1% Imp.

PRIMARY (H)	480 VOLTS (LINE-LINE)
SECONDARY (X)	240 VOLTS (LINE-LINE)
	120 VOLTS (1 PH MDTAP)



### COIL TAP ARRANGEMENT



JUMPER CONNECTION	
TAP	VOLTS
1-2	503
2-3	492
3-4	480
4-5	469
5-6	457
6-7	446
7-8	434

NET WGT  
1030 LB  
467.2 Kg

60439  
DY76A

NOG  
022516

INSPECTION  
&  
FINAL TEST  
N609!



Assembled in Mexico

X3 - X2 - X1 - X4  
- H3 - H2 - H1

Note: MID-TAP

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18W1076G06

REDUCED CAPACITY TAP RATED AT 5% OF 3 PH KVA

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

Outline:

ALUMINUM CONDUCTOR


PRIMARY: 10 KV BIL

SECONDARY: 10 KV BIL

303B111MWDYP76A

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES

CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODE



\*2M000000\*



\*3M000000\*

X3 - X2 - X1 -

H3 - H2 - H1

X3 - X2 - X1 -

H3 - H2 - H1