



Transformer



1M000000


Catalog Number
9T10X1004G61

Type **QL**

75.0 KVA 60 HZ 3 PH 3.2 % IMP

40 C AMB. 80 C RISE 220 C SYSTEM IS-19C

Note: Design is based on 112.5KVA & 150C Rise 5% Imp.



| JUMPER CONNECTION | |
|-------------------|-------|
| TAP | VOLTS |
| 1-2 | 503 |
| 2-3 | 492 |
| 3-4 | 480 |
| 4-5 | 469 |
| 5-6 | 457 |
| 6-7 | 446 |
| 7-8 | 435 |

NET WGT
790 LB
358.3 Kg


60472
DY75C

NOG
032816

INSPECTION
&
FINAL TEST
N614!

| | |
|---------------|--------------------------|
| PRIMARY (H) | 480 VOLTS (LINE-LINE) |
| SECONDARY (X) | 208 VOLTS (LINE-LINE) |
| | 120 VOLTS (LINE-NEUTRAL) |

COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18W1074G06

Assembled in Mexico

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

Outline:
303B111MWDYP75C

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODE

X3 - X2 - X1 - -
- H3 - H2 - H1

Note: X0 at the bottom



2M000000



3M000000

X3 - X2 - X1 - -
- H3 - H2 - H1
X3 - X2 - X1 - -
- H3 - H2 - H1

X0