



Transformer

by ABB



1M000000


Catalog Number **Type QL**
9T10C1882G61

30.0 KVA 60 HZ 3 PH 2.1 % IMP
40 C AMB. 80 C RISE 220 C SYSTEM IS-19C


Note: Design is based on 45.00KVA & 150C Rise 3.5% Imp.

PRIMARY (H) 440 VOLTS (LINE-LINE)
SECONDARY (X) 220 VOLTS (LINE-LINE)
127 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	TAP VOLTS
1	462
2	452
3	440
4	430
5	416
6	406
7	395



COIL TAP ARRANGEMENT



NET WGT	INSPECTION & FINAL TEST
480 LB	
217.7 Kg	NOG
88894	N137!
UX73C	091021



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

X3 H3 X2 H2 X1 H1 -
Note: X0 at the top

Outline: 303B111GEUXP73C

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

X0

X3	H3	X2	H2	X1	H1	-
X3	H3	X2	H2	X1	H1	-

2M000000

3M000000