



# Transformer

by ABB




\*1M000000\*

**Catalog Number** 9T10C2045      **Type** QL


**112.5 KVA**    **60 HZ**    **3 PH**    **5.7 % IMP**  
**40 C AMB.**    **150 C RISE**    **220 C SYSTEM**    **IS-19C**

**PRIMARY (H) 400 VOLTS (LINE-LINE)**  
**SECONDARY (X) 230 VOLTS (LINE-LINE)**  
**133 VOLTS (LINE-NEUTRAL)**

JUMPER CONNECTION	
TAP	VOLTS
1-2	421
2-3	409
3-4	400
4-5	387
5-6	382
6-7	371
7-8	360



**COIL TAP ARRANGEMENT**



**NET WGT**  
790 LB  
358.3 Kg  
89807  
DY75C

**INSPECTION & FINAL TEST**  
NOG  
N137!  
091021



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**

COPPER CONDUCTOR      PRIMARY: 10 KV BIL      SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.

CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

**ASSEMBLED IN MEXICO**

**X3 - X2 - X1 - -**  
**- H3 - H2 - H1**

Note: X0 at the bottom

Outline: 303B11GEDYP75C

**X3 - X2 - X1 - -**

**- H3 - H2 - H1**

**X3 - X2 - X1 - -**

**- H3 - H2 - H1**

**X0**