



Core & Coil Transformer

by ABB




1M000000

Catalog Number **Type QL-C**
9T10V1007G58


225.0 KVA 60 HZ 3 PH 4.3 % IMP
40 C AMB. 115 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 208 VOLTS (LINE-LINE)
120 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION	
TAP	VOLTS
1-2	508
2-3	490
3-4	480
4-5	471
5-6	453
6-7	443
7-8	434



COIL TAP ARRANGEMENT



NET WGT **INSPECTION**
1687 LB **& FINAL**
765.2 Kg **TEST**
89859 **NOG**
DX77C **N137!**
091021



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP009
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER


Meets DOE 2016 efficiency

Note:

Outline: 303B112GEDXP77C



2M000000



3M000000