



Transformer



1M0000000

Catalog Number
9T11A1007G33

Type QL


225.0 KVA 60 HZ 3 PH 4.5 % IMP

40 C AMB. 115 C RISE 220 C SYSTEM IS-19C


Note: Design is based on 300.0KVA & 150C Rise 5.5% Imp.

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 208 VOLTS (LINE-LINE)
120 VOLTS (LINE-NEUTRAL)

ELECTROSTATIC GROUND SHIELD IN EACH PHASE



COIL TAP ARRANGEMENT



| JUMPER CONNECTION | |
|-------------------|-------|
| TAP | VOLTS |
| 1-2 | 507 |
| 2-3 | 494 |
| 3-4 | 480 |
| 4-5 | 467 |
| 5-6 | 454 |
| 6-7 | 447 |
| 7-8 | 434 |

NET WGT
1670 LB
757.5 Kg

58585
DY78A

NOG
121315

INSPECTION
&
FINAL TEST
N551!



Assembled in Mexico

ENCLOSURE TYPE 2 (IP20) OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1077G06

SUITABLE FOR NONSINUSOIDAL CURRENT LOAD WITH K-FACTOR NOT TO EXCEED 13

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

ALUMINUM CONDUCTOR

PRIMARY: 10 KV BIL

SECONDARY: 10 KV BIL

Outline:

303B112GEDYP78A

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODE

