



Transformer

—
by ABB



1M000000


Catalog Number 9T11A1001G04 **Type** QL

15.0 KVA **60 HZ** **3 PH** **3.8 % IMP**
40 C AMB. **150 C RISE** **220 C SYSTEM** **IS-19C**


Note: Design is based on 15.00KVA & 115C Rise 3.5% Imp.

PRIMARY (H) **480 VOLTS (LINE-LINE)**
SECONDARY (X) **208 VOLTS (LINE-LINE)**
 120 VOLTS (LINE-NEUTRAL)

JUMPER CONNECTION TAP	VOLTS
1	504
2	493
3	480
4	468
5	455
6	445
7	432



COIL TAP ARRANGEMENT



NET WGT 231 LB
INSPECTION & FINAL TEST 104.8 Kg
NOG 89017
N139! UX71A
092021



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06
SUITABLE FOR NONSINUSOIDAL CURRENT LOAD WITH K-FACTOR NOT TO EXCEED 13

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.

CHECK ADDITIONAL NEC AND LOCAL CODE

ASSEMBLED IN MEXICO

X3 H3 X2 H2 X1 H1 X0

Note: standard

Outline: 303B111GEUXP71A

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

X0
X1
H1
X2
H2
X3
H3
X2
H2
X3
H3
X1
H1
X0



2M000000



3M000000