

**GE Transformer**

—  
**by ABB**



\*1M000000\*

**Catalog Number**      **Type QL**  
**9T11A1024G03**



**75.0 KVA    60 HZ    3 PH    2.8 % IMP**  
**40 C AMB.    150 C RISE    220 C SYSTEM    IS-19C**

*Note: Design is based on 112.5KVA & 150C Rise 4.2% Imp.*

**PRIMARY (H)    480 VOLTS (LINE-LINE)**  
**SECONDARY (X)    220 VOLTS (LINE-LINE)**  
**127 VOLTS (LINE-NEUTRAL)**

**JUMPER CONNECTION**

TAP	VOLTS
1-2	504
2-3	490
3-4	480
4-5	467
5-6	458
6-7	445
7-8	431



**NET WGT**  
680 LB  
308.4 Kg  
89106  
DY75A

**INSPECTION & FINAL TEST**  
NOG  
N137!  
091021



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

SUITABLE FOR NONSINUSOIDAL CURRENT LOAD WITH K-FACTOR NOT TO EXCEED 13

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

ALUMINUM CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.

CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

**ASSEMBLED IN MEXICO**

**X3 - X2 - X1 - -**

**- H3 - H2 - H1**

Note: X0 at the bottom

Outline: 303B11GEDYP75A

**X0**

- H1

- H2

- H3

- X1

- X2

- X3

\*2M000000\*

\*3M000000\*