



# Transformer



\*1M000000\*

Catalog Number  
**9T11C1354G03**

Type **QL**

**75.0 KVA 60 HZ 3 PH 3.6 % IMP**

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 208 VOLTS (LINE-LINE)  
SECONDARY (H) 380 VOLTS (LINE-LINE)  
219 VOLTS (LINE-NEUTRAL)

ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

SUITABLE FOR NONSINUSOIDAL CURRENT LOAD WITH K-FACTOR NOT TO EXCEED 13

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

COPPER CONDUCTOR

PRIMARY: 10 KV BIL


SECONDARY: 10 KV BIL

Outline:


303B111GEDYP75C

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES

CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODE



### COIL TAP ARRANGEMENT



JUMPER CONNECTION	
TAP	VOLTS
1-2	219
2-3	214
3-4	208
4-5	202
5-6	196
6-7	191
7-8	185

NET WGT  
790 LB  
358.3 Kg

60309  
DY75C  
NOG  
021016

INSPECTION  
&  
FINAL TEST  
N607!




Assembled in Mexico

H3 - H2 - H1 - -  
- X3 - X2 - X1

Note: H0 at the bottom

H3 - H2 - H1 - -  
- X3 - X2 - X1  
H3 - H2 - H1 - -  
- X3 - X2 - X1



\*2M000000\*



\*3M000000\*