



Transformer

by ABB



1M000000


Catalog Number 9T11C1413G03 **Type** QL

45.0 KVA 60 HZ 3 PH 2.4 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C


JUMPER CONNECTION

TAP	VOLTS
1	217
2	212
3	208
4	204
5	199

PRIMARY (X) 208 VOLTS (LINE-LINE)
 SECONDARY (H) 230 VOLTS (LINE-LINE)
 133 VOLTS (LINE-NEUTRAL)



COIL TAP ARRANGEMENT



NET WGT
 661 LB
 299.8 Kg
 89976 UY74C

INSPECTION & FINAL TEST
 NOG
 N139!
 092021



LISTED 769G

ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1074G06

SUITABLE FOR NONSINUSOIDAL CURRENT LOAD WITH K-FACTOR NOT TO EXCEED 13

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.

CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

H3 X3 H2 X2 H1 X1

Note: H0 at the bottom

Outline: 303B111GEUY74C

H3 X3 H2 X2 H1 X1
 - - - - -
 H3 X3 H2 X2 H1 X1
 - - - - -



2M000000



3M000000

H0