



# Transformer



\*1M000000\*


Catalog Number  
**9T14A1008G33**

Type **QL**

**300.0 KVA 60 HZ 3 PH 2.9 % IMP**

40 C AMB. 115 C RISE 220 C SYSTEM IS-19C

Note: Design is based on 500.0KVA & 115C Rise 4.8% Imp.



JUMPER CONNECTION	
TAP	VOLTS
1-2	500
2-3	490
3-4	480
4-5	470
5-6	460

NET WGT  
2900 LB  
1315.4 Kg

60390

DK79A


NOG

021716

INSPECTION  
&  
FINAL TEST  
N608!

PRIMARY (H)	480 VOLTS (LINE-LINE)
SECONDARY (X)	208 VOLTS (LINE-LINE)
	120 VOLTS (LINE-NEUTRAL)

### COIL TAP ARRANGEMENT



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1079G06

SUITABLE FOR NONSINUSOIDAL CURRENT LOAD WITH K-FACTOR NOT TO EXCEED 4

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

ALUMINUM CONDUCTOR

PRIMARY: 10 KV BIL

SECONDARY: 10 KV BIL

Outline:


303B112GEDXP79A

Assembled in Mexico


**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES**

**CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODE**

Note:



\*2M000000\*



\*3M000000\*