



# Transformer

by ABB



\*1M000000\*


**Catalog Number**      **Type QL**  
**9T14C1332G03**

30.0 KVA    60 HZ    3 PH    6.6 % IMP  
40 C AMB.    150 C RISE    220 C SYSTEM    IS-19C


*Note: Design is based on 30.00KVA & 150C Rise 6.6% Imp.*

PRIMARY (X)    208 VOLTS (LINE-LINE)  
SECONDARY (H)    480 VOLTS (LINE-LINE)

JUMPER CONNECTION TAP	VOLTS
1	218
2	214
3	208
4	202
5	198
6	192
7	188



### COIL TAP ARRANGEMENT



**NET WGT**  
353 LB  
160.1 Kg  
89698  
UX72C

**INSPECTION & FINAL TEST**  
NOG  
N139!  
092021



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

SUITABLE FOR NONSINUSOIDAL CURRENT LOAD WITH K-FACTOR NOT TO EXCEED 4

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

COPPER CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.

CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency

ASSEMBLED IN MEXICO

H3 X3 H2 X2 H1 X1 -

Note: standard


Outline: 303B111GEUXP72C

H3 X3 H2 X2 H1 X1



\*2M000000\*

H3 X3 H2 X2 H1 X1



\*3M000000\*