



Transformer


Catalog Number

TYPE QL

9T23B2671



25.0 KVA 60 HZ 1 PH 5.9 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C



PRIMARY LINES ON H1-H2				SECONDARY LINES ON X1-X4	
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT
217	8-H1, 7-H2	434	8-7	120	X1-X3, X2-X4
227	6-H1, 5-H2	443	7-6	240	X2-X3
240	4-H1, 3-H2	454	6-5		
253	2-H1, 1-H2	467	5-4		
		480	4-3		
		493	3-2		

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B904AAP071

INSPECTION &
FINAL TEST
N731&

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

080107

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

NET WGT
185 LB

Assembled in Mexico 949



1M0000000



2M0000000



2M0000000