



Transformer

Catalog Number TYPE QL


9T23B2681

25.0 KVA 60 HZ 1 PH 5.8 % IMP


40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY LINES ON H1-H2			
VOLTS	CONNECT	VOLTS	CONNECT
271	8-H1,7-H2	542	8-7
284	6-H1,5-H2	555	7-6
300	4-H1,3-H2	568	6-5
316	2-H1,1-H2	584	5-4
		600	4-3
		616	3-2

SECONDARY LINES ON X1-X4	
VOLTS	CONNECT
120	X1-X3,X2-X4
240	X2-X3



COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G05

Outline: 303B904AAP071

INSPECTION &
FINAL TEST
N731&

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

080107
NET WGT
185 LB

58

