



Transformer

by ABB




1M000000

Catalog Number

Type QL

9T33A2670

15.0 KVA 60 HZ 1 PH 4.7 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C




| PRIMARY LINES ON H1-H2 | | SECONDARY LINES ON X1-X4 | |
|---------------------------|-----------|-----------------------------|--------------------------------|
| VOLTS | CONNECT | VOLTS | CONNECT |
| 216 | 8-H1,7-H2 | 432 | 8-7 |
| 228 | 6-H1,5-H2 | 444 | 7-6 |
| 240 | 4-H1,3-H2 | 456 | 6-5 |
| 252 | 2-H1,1-H2 | 468 | 5-4 |
| | | 480 | 4-3 |
| | | 492 | 3-2 |
| | | 504 | 2-1 |
| | | | SECONDARY LINES ON X1-X2-X4 |
| | | | VOLTS CONNECT |
| | | | 120/240 X2-X3 |

NET WGT NOG
320 LB O91021
145.2 Kg INSPECTION
90121 &
YX171 FINAL TEST
 N137!



COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**

ASSEMBLED IN MEXICO

X3 - X1 - X2 X4
- H2 - H1 - -

Note:

Outline: 303B409CAP071

NEMA CLASS AA DRY TYPE TRANSFORMER

Energy Efficiency in accordance with CSA C802.2-18 and DOE 2016

| | | | | | |
|----|----|----|----|----|----|
| X3 | - | X1 | - | X2 | X4 |
| - | H2 | - | H1 | - | - |

2M0000000*

3M0000000*