




Transformer

Catalog Number TYPE QL

9T23B2673G03

50.0 KVA 60 HZ 1 PH 4.8 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C





ELECTROSTATIC GROUND SHIELD IN EACH PHASE

| PRIMARY LINES ON H1-H2 | | | |
|------------------------|------------|-------|---------|
| VOLTS | CONNECT | VOLTS | CONNECT |
| 214 | 8-H1, 7-H2 | 428 | 8-7 |
| 227 | 6-H1, 5-H2 | 441 | 7-6 |
| 240 | 4-H1, 3-H2 | 454 | 6-5 |
| 257 | 2-H1, 1-H2 | 467 | 5-4 |
| | | 480 | 4-3 |
| | | 497 | 3-2 |

| SECONDARY LINES ON X1-X4 | |
|--------------------------|--------------|
| VOLTS | CONNECT |
| 120 | X1-X3, X2-X4 |
| 240 | X2-X3 |

COIL TAP ARRANGEMENT



LISTED 769G

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G06

Outline: 303B904AAP073

INSPECTION & FINAL TEST N731&


BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

080107

NET WGT 340 LB

Assembled in Mexico 954



1M0000000



2M0000000



2M0000000