



Transformer

by ABB





1M000000


Catalog Number **9T33A2671** Type QL

25.0 KVA 60 HZ 1 PH 5.3 % IMP
 40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY LINES ON H1-H2		SECONDARY LINES ON X1-X4			
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT
217	8-H1,7-H2	434	8-7	120	X1-X3,X2-X4
229	6-H1,5-H2	446	7-6	240	X2-X3
240	4-H1,3-H2	457	6-5		
251	2-H1,1-H2	469	5-4		
		480	4-3		
		491	3-2		
		503	2-1	120/240	X2-X3



COIL TAP ARRANGEMENT



NET WGT 320 LB
 145.2 Kg
 90122
 YX171

NOG O91021
 INSPECTION &
 FINAL TEST
 NI37!



X4
 X2
 X1
 H1
 H2
 X4
 X2
 X1
 H1
 H2

ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
 ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
 CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**

ASSEMBLED IN MEXICO

X3 - X1 - X2 X4
 - H2 - H1 - -

Note:

Outline: 303B409CAP071

NEMA CLASS AA DRY TYPE TRANSFORMER

Energy Efficiency in accordance with CSA C802.2-18 and DOE 2016

