



# Transformer

by ABB




\*1M000000\*


Catalog Number **9T33C2671** Type QL

25.0 KVA 60 HZ 1 PH 4.5 % IMP  
 40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY LINES ON H1-H2		SECONDARY LINES ON X1-X4	
VOLTS	CONNECT	VOLTS	CONNECT
217	8-H1,7-H2	434	8-7
229	6-H1,5-H2	446	7-6
240	4-H1,3-H2	457	6-5
251	2-H1,1-H2	469	5-4
		480	4-3
		491	3-2
		503	2-1
			SECONDARY LINES ON X1-X2-X4
			VOLTS CONNECT
			120/240 X2-X3



### COIL TAP ARRANGEMENT



NET WGT 350 LB  
 158.8 Kg  
 90128  
 YX171

NOG O91021  
 INSPECTION &  
 FINAL TEST  
 NI37!



X4  
 X2  
 H1  
 X1  
 H2  
 X3  
 H1  
 X4  
 X2  
 H1

ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES  
 CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**

ASSEMBLED IN MEXICO

X3 - X1 - X2 X4  
 - H2 - H1 - -

Note:

Outline: 303B409CAP071

NEMA CLASS AA DRY TYPE TRANSFORMER

Energy Efficiency in accordance with CSA C802.2-18 and DOE 2016

