



Transformer

by ABB



1M000000


Catalog Number

9T33A2674G80

Type QL


75.0 KVA 60 HZ 1 PH 4.4 % IMP
40 C AMB. 80 C RISE 220 C SYSTEM IS-19C

NET WGT NOG
950 LB 091321
430.9 Kg INSPECTION
90126 &
YX175 FINAL TEST
N230@



PRIMARY LINES ON H1-H4		SECONDARY LINES ON X1-X4		SECONDARY LINES ON X1-X2-X4	
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT
214	7-8	428	7-8	120	X1-X3,X2-X4
230	5-6	449	6-7	240	X2-X3
240	3-4	459	5-6		
250	1-2	470	4-5		
		491	2-3		
		501	1-2	120/240	X2-X3

COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y4322G77

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

Note:

Outline: 303B409CAP075

NEMA CLASS AA DRY TYPE TRANSFORMER

Energy Efficiency in accordance with CSA C802.2-18 and DOE 2016



2M000000



3M000000