



Transformer



by ABB



1M000000


Catalog Number **9T33A2675** Type QL
 100.0 KVA 60 HZ 1 PH 5.8 % IMP
 40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY LINES ON H1-H4		SECONDARY LINES ON X1-X4	
VOLTS	CONNECT	VOLTS	CONNECT
214	H1-H3, H2-H4	428	7-8
230	5-6	449	6-7
240	3-4	459	5-6
250	1-2	480	3-4
		491	2-3
		501	1-2
		120	X1-X3, X2-X4
		240	X2-X3
		SECONDARY LINES ON X1-X2-X4	
		120/240	X2-X3



NET WGT 950 LB
 430.9 Kg
 90126
 YX175

NOG O91021
 INSPECTION &
 FINAL TEST
 NI37!



ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

ASSEMBLED IN MEXICO


BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP009
 ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
 CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**

Note:
 Outline: 303B409CAP075

NEMA CLASS AA DRY TYPE TRANSFORMER Energy Efficiency in accordance with CSA C802.2-18 and DOE 2016



2M000000



3M000000