



Specialty Transformer  
PO Box 1701  
Ft. Wayne, IN 46801  
(260) 439-2000

**GE MODEL #:**  
**9T45G0007G81**

Underwriters' Laboratories Inc Listed

**RATING:**

TFM CU 225 kVA 480(+2,-42.5%) - 208Y/120 80 C-rise ENERGY\$AVER

Frame =	FC78	Type TM
Temp. Rise (C) =	80	Insulation System = 220C
Average Sound Level (dB) =	54	@ 50% load & below.
	65	@ over 50% load.

**LOSS DATA:**

Core Loss or No Load Loss @ 100% voltage (Watts) =	500.0
Impedance Loss or Coil Loss @ Rise + 20C reference (Watts) =	4470.0
Total Loss @ Rise + 20C reference (Watts) =	4970.0

**DIELECTRIC AND PRODUCTION TESTING:**

Induce Test @ Twice rated voltage 400 Hz per ANSI C89.2 and NEMA ST-20  
 Hipot Test for High Voltage winding to Low Voltage and Ground @ 4000 volts 60 Hz 60 Sec.  
 Hipot Test for Low Voltage winding to Ground @ 2500 volts 60 Hz 60 Sec.  
 Polarity additive in accordance with ANSI C89.2 and NEMA ST-20

**EFFICIENCY:**

Efficiencies at reference temperature of Rise + 20C (Calculated).

Load (%)	Efficiency (%)
25	98.7
35	98.8
50	98.6
75	98.4
100	97.9

Complies with NEMA TP-1

**IMPEDANCE:**

Impedance at reference temperature of Rise + 20C (Calculated).

%R =	2.0
%X =	3.8
%Z =	4.3

**REGULATION:**

Regulation at reference temperature of Rise + 20C (Calculated).

PF	Regulation (%)
1.0	2.0
0.8	3.8