



Transformer

by ABB




1M00046K2


Catalog Number **9T33C2670** Type QL

15.0 KVA 60 HZ 1 PH 4.2 % IMP
 40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY LINES ON H1-H2		SECONDARY LINES ON X1-X4			
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT
216	8-H1,7-H2	432	8-7	120	X1-X3,X2-X4
228	6-H1,5-H2	444	7-6	240	X2-X3
240	4-H1,3-H2	456	6-5		
252	2-H1,1-H2	468	5-4	SECONDARY	
		480	4-3	LINES ON X1-X2-X4	
		492	3-2	VOLTS	CONNECT
		504	2-1	120/240	X2-X3



COIL TAP ARRANGEMENT



NET WGT 350 LB
 158.8 Kg
 O

NOG 1203202
 INSPECTION &
 FINAL TEST
 NO49&



ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9. ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

ASSEMBLED IN MEXICO

X3 X1 - X2 X4 -
 - - H2 - - H1

Note:

Outline: 303B409CAP071

NEMA CLASS AA DRY TYPE TRANSFORMER

Energy Efficiency in accordance with CSA C802.2-18 and DOE 2016

X4 - H1
 X4 - H1
 X2 - H2
 X2 - H2
 X1 - H2
 X1 - H2
 X3 - H2
 X3 - H2

2M00046K2

3M00046K2

