



Transformer

by ABB



1M000000


Catalog Number

9T33C2670G15



Type QL

15.0 KVA 60 HZ 1 PH 4 % IMP
40 C AMB. 115 C RISE 220 C SYSTEM IS-19C

PRIMARY			SECONDARY		
LINES ON H1-H2			LINES ON X1-X4		
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT
216	8-H1,7-H2	432	8-7	120	X1-X3,X2-X4
228	6-H1,5-H2	444	7-6	240	X2-X3
240	4-H1,3-H2	456	6-5		
252	2-H1,1-H2	468	5-4		
		480	4-3		
		492	3-2		
		504	2-1		
				SECONDARY	
				LINES ON X1-X2-X4	
				VOLTS	CONNECT
				120/240	X2-X3



COIL TAP ARRANGEMENT



NET WGT	NP3
350 LB	O33122
158.8 Kg	INSPECTION
90127	&
	FINAL TEST
YX171	N214@



X4
X2
X1 - H1
X1 - H1
H2
X3 - H2
X3 - H2

ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

ASSEMBLED IN MEXICO

X3 - X1 - X2 X4
- H2 - H1 - -

Note:

Outline: 303B409CAP071

NEMA CLASS AA DRY TYPE TRANSFORMER

Energy Efficiency in accordance with CSA C802.2-18 and DOE 2016



2M000000



3M000000