



Transformer

by ABB




1M000000


Catalog Number **9T33C2672** Type QL

37.5 KVA 60 HZ 1 PH 6 % IMP
 40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY LINES ON H1-H2		SECONDARY LINES ON X1-X4	
VOLTS	CONNECT	VOLTS	CONNECT
216	8-H1,7-H2	432	8-7
226	6-H1,5-H2	442	7-6
240	4-H1,3-H2	453	6-5
254	2-H1,1-H2	466	5-4
		480	4-3
		494	3-2
		507	2-1



COIL TAP ARRANGEMENT



ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
 CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**

NEMA CLASS AA DRY TYPE TRANSFORMER

Energy Efficiency in accordance with CSA C802.2-18 and DOE 2016

NET WGT 510 LB
 231.3 Kg
 YX172

NOG O91021
 INSPECTION &
 FINAL TEST N137!



X4 - - -
 X2 - - -
 H1 - - -

X1 - - -
 H2 - - -

X3 - - -
 X3 - - -



ASSEMBLED IN MEXICO

X3 - X1 - X2 - X4
 - H2 - H1 - - -
 Note:

Outline: 303B409CAP072