



Transformer

by ABB




1M00046K0


Catalog Number **9T33C2672** Type QL

37.5 KVA 60 HZ 1 PH 6 % IMP
 40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY LINES ON H1-H2		SECONDARY LINES ON X1-X4			
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT
216	8-H1,7-H2	432	8-7	120	X1-X3,X2-X4
226	6-H1,5-H2	442	7-6	240	X2-X3
240	4-H1,3-H2	453	6-5		
254	2-H1,1-H2	466	5-4		
		480	4-3		
		494	3-2		
		507	2-1	120/240	X2-X3



COIL TAP ARRANGEMENT



NET WGT 510 LB
 231.3 Kg
 O

NOG 1203202
 INSPECTION &
 FINAL TEST
 NO49&



ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9. ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

ASSEMBLED IN MEXICO

X3 - X1 - X2 - X4
 - H2 - H1 - - -
 Note:

Outline: 303B409CAP072

NEMA CLASS AA DRY TYPE TRANSFORMER

Energy Efficiency in accordance with CSA C802.2-18 and DOE 2016

X4	.	X4	.
X2	.	X2	.
X1	.	X1	.
H1	.	H1	.
X3	.	X3	.
H2	.	H2	.

2M00046K0

3M00046K0



TRANSFORMATEUR


by ABB




1M00046K0

No. Catalogue **9T33C2672** Type QL
 37.5 KVA 60 HZ 1 PH 6 % IMP
 40 C AMB. 150 ÉLÉV. TEMP. 220 CLASS D'ISOL. IS-19C

PRIMARY LINES ON H1-H2		SECONDARY LINES ON X1-X4	
VOLTS	CONNECT	VOLTS	CONNECT
216	8-H1,7-H2	432	8-7
226	6-H1,5-H2	442	7-6
240	4-H1,3-H2	453	6-5
254	2-H1,1-H2	466	5-4
		480	4-3
		494	3-2
		507	2-1
			SECONDARY LINES ON X1-X2-X4 VOLTS CONNECT 120/240 X2-X3



ENSEMBLE DE PRISE D'ENROULEMENT



POIDS NET 510 LB
 231.3 Kg
 O

NOG 1203202
 INSPECTION & ESSAIS FINAUX
 NO49&



X4 - .

X2 - .

H1 - .

X1 - .

H2 - .

X3 - .

X1 - .

X2 - .

X3 - .

X4 - .

BOÎTIER TYPE 2(IP20) À L'ÉPREUVE DES ÉGOUTTEMENTS. BOÎTIER TYPE 3R (IP22). À L'ÉPREUVE DES INTEMPÉRIES LORSQUE FOURNI AVEC ÉCRAN 9T18Y1071G06

VOIR INSTRUCTION 475A667AAP001 AVANT LA MANIPULATION, L'INSTALLATION OU L'OPÉRATION

COPPER CONDUCTEUR PRIMAIRE: 10 KV BIL SECONDAIRE: 10 KV BIL

LAISSER UNE ESPACE DE 6 POUCHES POUR ASSURER UNE VENTILATION ADÉQUATE. VÉRIFIER LES CONSIGNES DU CODE ÉLECTRIQUE CANADIEN OU AUTRES CODES.

TRANSFORMATEUR À SEC NEMA CLASSE AA

Conforme au rendement DOE 2016

ASSEMBLÉ AU MEXIQUE

X3 - X1 - X2 - X4
 - H2 - H1 - - -
 Note:

Schéma: 303B409CAP072

Conforme au CSA C802.2-18



2M00046K0



3M00046K0