



Transformer

by ABB



1M000000



Catalog Number

Type QL


9T33C2673

50.0 KVA 60 HZ 1 PH 4.7 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY		SECONDARY	
LINES ON H1-H2		LINES ON X1-X4	
VOLTS	CONNECT	VOLTS	CONNECT
215	8-H1,7-H2	430	8-7
227	6-H1,5-H2	442	7-6
240	4-H1,3-H2	454	6-5
253	2-H1,1-H2	467	5-4
	480	4-3	SECONDARY
	493	3-2	LINES ON X1-X2-X4
	506	2-1	VOLTS CONNECT
		120/240	X2-X3



COIL TAP ARRANGEMENT



NET WGT 500 LB
500 LB
226.8 Kg
90130
XV173

NOG O91021
INSPECTION &
FINAL TEST
N137!



X4	-	H1
X2	-	H1
X1	-	H2
X3	-	H2
X4	-	H1
X2	-	H1
X1	-	H2
X3	-	H2

ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

ASSEMBLED IN MEXICO

X3 X1 - X2 X4 - -
- - H2 - - H1

Note: Standard

Outline: 303B409CAP073

NEMA CLASS AA DRY TYPE TRANSFORMER

Energy Efficiency in accordance with CSA C802.2-18 and DOE 2016

