



# Transformer

by ABB




\*1M00046JZ\*


Catalog Number **9T33C2674** Type QL

75.0 KVA 60 HZ 1 PH 5.9 % IMP  
 40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY LINES ON H1-H4		SECONDARY LINES ON X1-X4	
VOLTS	CONNECT	VOLTS	CONNECT
216	H1-H3, H2-H4	432	7-8
230	7-8	446	6-7
240	5-6	461	5-6
240	3-4	470	4-5
250	1-2	480	3-4
		490	2-3
		499	1-2
		SECONDARY LINES ON X1-X2-X4	
		VOLTS	CONNECT
		120/240	X2-X3



### COIL TAP ARRANGEMENT



NET WGT 750 LB  
 340.2 Kg  
 O

NP1 1203202  
 INSPECTION &  
 FINAL TEST  
 N934!



ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL  
**IN ACCORDANCE WITH NEC SECTION 450-9. ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**

ASSEMBLED IN MEXICO

X3 - X1 - X2 X4  
 - - H4 - H1 - -  
 Note:

Outline: 303B409CAP074

NEMA CLASS AA DRY TYPE TRANSFORMER

Energy Efficiency in accordance with CSA C802.2-18 and DOE 2016

X4 - .

X2 - .

X1 - .

H1 - .

H4 - .

X3 - .

X3 - .

X2 X4 - .

X1 - .

H1 - .

X3 - .

H4 - .

X3 - .

H4 - .

\*2M00046JZ\*

\*3M00046JZ\*



# TRANSFORMATEUR

by ABB




\*1M00046JZ\*

No. Catalogue **9T33C2674** Type QL


75.0 KVA 60 HZ 1 PH 6.0 % IMP

40 C AMB. 150 ÉLÉV. TEMP. 220 CLASS D'ISOL. IS-19C

PRIMARY LINES ON H1-H4		SECONDARY LINES ON X1-X4	
VOLTS	CONNECT	VOLTS	CONNECT
216	H1-H3,H2-H4 7-8	432	7-8
230	5-6	461	6-7
240	3-4	470	5-6
250	1-2	480	4-5
		490	3-4
		499	2-3
			1-2
		SECONDARY LINES ON X1-X2-X4	
		VOLTS	CONNECT
		120	X1-X3,X2-X4
		240	X2-X3
		120/240	X2-X3



### ENSEMBLE DE PRISE D'ENROULEMENT



POIDS NET NP1  
750 LB 1203202  
340.2 Kg INSPECTION &  
O ESSAIS  
FINAUX  
N934!



BOÎTIER TYPE 2(IP20) À L'ÉPREUVE DES ÉGOUTTEMENTS. BOÎTIER TYPE 3R (IP22). À L'ÉPREUVE DES INTEMPÉRIES LORSQUE FOURNI AVEC ÉCRAN 9T18Y1071G06

VOIR INSTRUCTION 475A667AAP001 AVANT LA MANIPULATION, L'INSTALLATION OU L'OPÉRATION

COPPER CONDUCTEUR      PRIMAIRE: 10 KV BIL      SECONDAIRE: 10 KV BIL

**LAISSER UNE ESPACE DE 6 POUÇES POUR ASSURER UNE VENTILATION ADÉQUATE. VÉRIFIER LES CONSIGNES DU CODE ÉLECTRIQUE CANADIEN OU AUTRES CODES.**

TRANSFORMATEUR À SEC NEMA CLASSE AA

Conforme au rendement DOE 2016

### ASSEMBLÉ AU MEXIQUE

X3 - X1 - X2 X4

- H4 - H1 -

Note:

Schéma: 303B409CAP074

Conforme au CSA C802.2-18

X4	-	-	-
X2	-	-	X4
H1	-	X2	-
X1	-	-	H1
H4	-	X1	-
X3	-	H4	-
X3	-	-	H4



\*2M00046JZ\*



\*3M00046JZ\*