



Transformer


by ABB




1M000000

Catalog Number **9T33C2674** Type QL
 75.0 KVA 60 HZ 1 PH 5.9% IMP
 40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY LINES ON H1-H4			SECONDARY LINES ON X1-X4		
VOLTS	CONNECT	VOLTS	CONNECT	VOLTS	CONNECT
216	H1-H3, H2-H4	432	7-8	120	X1-X3, X2-X4
230	5-6	461	5-6	240	X2-X3
240	3-4	470	4-5		
250	1-2	480	3-4		
		490	2-3		
		499	1-2	120/240	X2-X3




COIL TAP ARRANGEMENT



NET WGT 750 LB
 340.2 Kg
 90131
 YX174

NOG 091021
 INSPECTION &
 FINAL TEST
 NI137!



ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18Y1071G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.

ASSEMBLED IN MEXICO

X3 - X1 - X2 X4

Note:

Outline: 303B409CAP074

NEMA CLASS AA DRY TYPE TRANSFORMER

Energy Efficiency in accordance with CSA C802.2-18 and DOE 2016

X4
 - X2 -
 - H1 -

X1
 - X1 - X2 X4
 - H4 - H1

X3
 - X3 - X1 - X2 X4
 - H4 - H1

