



K Factor Transformer

Catalog Number 9T61B5807G03


9Q3A225ABBR13A2T00

225.0 KVA 60 HZ 3 PH 3 % IMP

40 C AMB. 150 C RISE 220 C SYSTEM IS-19C Type: QL


PRIMARY (H)	460 VOLTS (LINE-LINE)
SECONDARY (X)	460 VOLTS (LINE-LINE)
	266 VOLTS (LINE-NEUTRAL)

ELECTROSTATIC GROUND SHIELD IN EACH PHASE



JUMPER CONNECTION	
TAP	VOLTS
1-2	484
2-3	469
3-4	460
4-5	445
5-6	437
6-7	422
7-8	414

COIL TAP ARRANGEMENT



NET WGT 3400 LB 1542.2 Kg

120115 N549! YF379

58456 NOG

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4322G68

SUITABLE FOR NONSINUSOIDAL CURRENT LOAD WITH K-FACTOR NOT TO EXCEED 13 BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.



Outline: 303B919AAP179
Assembled in Mexico

INSPECTION & FINAL TEST
N549!

