



# Transformer

Catalog Number 9T61C9567G23

**9Q3C225AAP13B2T30**

**225.0 KVA 60 HZ 3 PH 1.7 % IMP**

40 C AMB. 115 C RISE 220 C SYSTEM IS-19C Type: QL

Note: Design is based on 500.0KVA & 150C Rise 3.9% Imp.

PRIMARY (H) 480 VOLTS (LINE-LINE)

SECONDARY (X) 480 VOLTS (LINE-LINE)

ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4322G68


SUITABLE FOR NONSINUSOIDAL CURRENT LOAD WITH K-FACTOR NOT TO EXCEED 13  
BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES  
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**


GE Energy Industrial Solutions

**NEMA CLASS AA DRY TYPE TRANSFORMER**

Meets TP-1 2002 efficiency



### COIL TAP ARRANGEMENT



### JUMPER CONNECTION

TAP	VOLTS
1-2	502
2-3	491
3-4	480
4-5	469
5-6	458
6-7	447
7-8	436

NET WGT 4050 LB 1837.1 Kg

090115 N536! YF379

55809 NOG



LISTED 769G

Outline: 3038919AAP179

Assembled in Mexico

INSPECTION & FINAL TEST

N536!

