



Transformer

Catalog Number 9T64C9388G13

9Q3C300AAAZ04B2T00

300.0 KVA 60 HZ 3 PH 2.8 % IMP

40 C AMB. 115 C RISE 220 C SYSTEM IS-19C Type: QL

Note: Design is based on 500.0KVA & 150C Rise 4.7% Imp.

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 220 VOLTS (LINE-LINE)
127 VOLTS (LINE-NEUTRAL)

ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4322G68


SUITABLE FOR NONSINUSOIDAL CURRENT LOAD WITH K-FACTOR NOT TO EXCEED 4
BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**

GE Energy Industrial Solutions


NEMA CLASS AA DRY TYPE TRANSFORMER

Meets TP-1 2002 efficiency



JUMPER CONNECTION	
TAP	VOLTS
1-2	508
2-3	487
3-4	480
4-5	466
5-6	455
6-7	445
7-8	434

COIL TAP ARRANGEMENT



NET WGT 4050 LB 1837.1 Kg

090115 N536! YF379

55784 NOG



LISTED 769G

Outline: 3038919AAP179
Assembled in Mexico

INSPECTION & FINAL TEST
N536!

