



Specialty Transformer
PO Box 1701
Ft. Wayne, IN 46801
(260) 439-2000

GE MODEL #:
9T43G0006G53

Underwriters' Laboratories Inc Listed

RATING:

TFM AL 150 kVA 480(+2,-42.6%) - 208Y/120 115 C-rise NON-SIN K=30

Frame =	FC78	Type	TM
Temp. Rise (C) =	115	Insulation System =	220C
Average Sound Level (dB) =	54	@ 50% load & below.	
	65	@ over 50% load.	

LOSS DATA:

Core Loss or No Load Loss @ 100% voltage (Watts) =	500.0
Impedance Loss or Coil Loss @ Rise + 20C reference (Watts) =	<u>2130.0</u>
Total Loss @ Rise + 20C reference (Watts) =	2630.0

DIELECTRIC AND PRODUCTION TESTING:

Induce Test @ Twice rated voltage 400 Hz per ANSI C89.2 and NEMA ST-20
 Hipot Test for High Voltage winding to Low Voltage and Ground @ 4000 volts 60 Hz 60 Sec.
 Hipot Test for Low Voltage winding to Ground @ 2500 volts 60 Hz 60 Sec.
 Polarity additive in accordance with ANSI C89.2 and NEMA ST-20

EFFICIENCY:

Efficiencies at reference temperature of Rise + 20C (Calculated).

Load (%)	Efficiency (%)
25	98.4
35	98.7
50	98.7
75	98.6
100	98.3

Complies with NEMA TP-1

IMPEDANCE:

Impedance at reference temperature of Rise + 20C (Calculated).

%R =	1.8
%X =	2.9
%Z =	3.4

REGULATION:

Regulation at reference temperature of Rise + 20C (Calculated).

PF	Regulation (%)
1.0	1.7
0.8	3.0