



Specialty Transformer
PO Box 1701
Ft. Wayne, IN 46801
(260) 439-2000

GE MODEL #:
9T46G0006G03

Underwriters' Laboratories Inc Listed

RATING:

TFM CU 150 kVA 480(+2,-42.4%) - 208Y/120 150 C-rise NON-SIN K=13

Frame =	FC77	Type	TM
Temp. Rise (C) =	150	Insulation System =	220C
Average Sound Level (dB) =	54	@ 50% load & below.	
	65	@ over 50% load.	

LOSS DATA:

Core Loss or No Load Loss @ 100% voltage (Watts) =	400.0
Impedance Loss or Coil Loss @ Rise + 20C reference (Watts) =	3025.0
Total Loss @ Rise + 20C reference (Watts) =	3425.0

DIELECTRIC AND PRODUCTION TESTING:

Induce Test @ Twice rated voltage 400 Hz per ANSI C89.2 and NEMA ST-20
 Hipot Test for High Voltage winding to Low Voltage and Ground @ 4000 volts 60 Hz 60 Sec.
 Hipot Test for Low Voltage winding to Ground @ 2500 volts 60 Hz 60 Sec.
 Polarity additive in accordance with ANSI C89.2 and NEMA ST-20

EFFICIENCY:

Efficiencies at reference temperature of Rise + 20C (Calculated).

Load (%)	Efficiency (%)
25	98.5
35	98.7
50	98.5
75	98.3
100	97.8

Complies with NEMA TP-1

IMPEDANCE:

Impedance at reference temperature of Rise + 20C (Calculated).

%R =	2.1
%X =	3.3
%Z =	3.9

REGULATION:

Regulation at reference temperature of Rise + 20C (Calculated).

PF	Regulation (%)
1.0	2.0
0.8	3.5