



Transformer



1M000000

Catalog Number **Type** QL
9Q3C015AFAP13B2T00
9T61C9031G13

15.0 KVA 60 HZ 3 PH 4.3 % IMP

40 C AMB. 115 C RISE 220 C SYSTEM IS-19C

Note: Design is based on 15.00KVA & 150C Rise 4.5% Imp.

PRIMARY (X) 208 VOLTS (LINE-LINE)
 SECONDARY (H) 480 VOLTS (LINE-LINE)

ELECTROSTATIC GROUND SHIELD IN EACH PHASE


ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4317G11
 SUITABLE FOR NONSINUSOIDAL CURRENT LOAD WITH K-FACTOR NOT TO EXCEED 13
 BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001 Outline: 303B401AAP071
 COPPER CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
 CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**


GE Energy Industrial Solutions

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets TP-1 2002 efficiency



COIL TAP ARRANGEMENT



JUMPER CONNECTION	
TAP	VOLTS
1	218
2	214
3	208
4	204
5	197
6	192
7	187

NET WGT
 250 LB
 113.4 Kg

25056
 XV371
 NOG
 071615

INSPECTION
 &
 FINAL TEST
 N529!




LISTED 769G

Assembled in Mexico


H3 - H2 - H1 - -
 - X3 - X2 - X1

Note: Standard

H3 - H2 - H1 -
 - X3 - X2 - X1



2M000000



3M000000