



# Transformer

Catalog Number  
9T76H9872G03


30.0 KVA    60 HZ    3 PH    3.2 % IMP

40 C AMB.    150 C RISE    220 C SYSTEM    IS-19C    Type: QL

Note: Design is based on 30.00KVA & 115C Rise 3% Imp.


PRIMARY (H)    480 VOLTS (LINE-LINE)  
SECONDARY (X)    208 VOLTS (LINE-LINE)  
                          120 VOLTS (LINE-NEUTRAL)

ELECTROSTATIC GROUND SHIELD IN EACH PHASE



JUMPER CONNECTION TAP	VOLTS
1	505
2	492
3	480
4	469
5	456
6	442
7	433

### COIL TAP ARRANGEMENT



NET WGT 495 LB    224.5 Kg

041116    N616!    H372C  
60840    NOG

ENCLOSURE TYPE 2 (IP20). RAINPROOF TYPE 3R. ENCLOSURE (IP22) WHEN PROVIDED SHIELD 9T18V4317G06

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001  
COPPER CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**



LISTED 769G

Outline: 3038431SLP072  
Assembled in Mexico

INSPECTION & FINAL TEST  
N616!

GE Energy Industrial Solutions

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



\*1M0000000\*



\*3M0000000\*