



Transformer

Catalog Number

9T64B3148G03

300.0 KVA 60 HZ 3 PH 2.6 % IMP

40 C AMB. 115 C RISE 220 C SYSTEM IS-19C Type: QL

Note: Design is based on 500.0KVA & 150C Rise 3.7% Imp.


9T61B38776239T61B3877623

150910IG2 303B912HAP278 YNNN 40115


220IS-19CQL 3 60AL101034Y225.0 4 14

70 480(+2,-4 2.6

ELECTROSTATIC GROUND SHIELD IN EACH PHASE



COIL TAP ARRANGEMENT



NSALE0 225.000480C
+2,-4 2.60%)
208Y/120

0911

NN

N9T18Y4322G88T
TRANSFORMER N
ON-SIN K=13H0
0

520

NET WGT 3400 LB 1542.2 Kg

091015

N537!

S39AC

33255

NOG

ENCLOSURE TYPE 2 (IP30). RAINPROOF TYPE 3R ENCLOSURE (IP32) WHEN PROVIDED SHIELD 9T18Y4322G68

SUITABLE FOR NONSINUSOIDAL CURRENT LOAD WITH K-FACTOR NOT TO EXCEED 4
BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL

**IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES
CLEARANCE FOR VENTILATION. CHECK ADDITIONAL NEC AND LOCAL CODES.**



LISTED 769G

Outline: 303B918AAP079

Assembled in Mexico

INSPECTION & FINAL TEST

N537!



1M000000



3M000000